


Name of the Equipment / Facility	WALK-IN-CHAMBERS
Purpose of Use	To Simulate High Temperature and Damp Heat Environment
Photograph	
Key Specifications	<ul style="list-style-type: none"> ❖ MAKE : WEISS TECHNIK ❖ Temperature Range ; 0 to + 100⁰C ❖ Relative Humidity Range : 10 – 97 % ❖ Size of the chamber : 12000 x 3400 x 3400 mm ❖ Specimen Weight : 3000 kg ❖ Port Holes : 50 mm, 100mm & 150 mm dia ❖ Rate : 1⁰C/ min
Representative Output (if Possible)	Temperature and Humidity